



RATED VOLTAGE	12V DC
RATED POWER	30 W
RATED SPEED	3000 rpm
NUMBER OF POLE PAIRS	4
ENCODER	500 line
REDUCTION RATIO	50.9:1

SIGNAL	U	V	W		+	-	Ha	Hb	Hc	A	B	Z
COLOUR	YE	BU	GN	YE/GN	RD	BK	PL	WH	OG	YE	BU	GN
WIRE	22AWG			26AWG								

						 BLDC Brushless DC Motor Ningbo BLDC Co.,Ltd	NAME	BLDC MOTOR		
							PART NO.			
						DRW NO	B433030S12-C21RRP51K			
						MATERIAL	/			
						WEIGHT	/	PAGE	/	
MRK	DESCRIPTION	SIGNATURE	DATE	TOLERANCE	VIEW ANGLE					
DSGN		APRV		X ± 1						
CHCK		DATE		X.X ± 0.5		SCALE	1:1.5			
				X.XX ± 0.25						