

## 1. Description


### 1.1. Project

Project Name	stm32f105_1
Board Name	custom
Generated with:	STM32CubeMX 5.3.0
Date	08/10/2020

### 1.2. MCU

MCU Series	STM32F1
MCU Line	STM32F105/107
MCU name	STM32F105RBTx
MCU Package	LQFP64
MCU Pin number	64

## 2. Pinout Configuration




### 3. Pins Configuration

Pin Number LQFP64	Pin Name (function after reset)	Pin Type	Alternate Function(s)	Label
1	VBAT	Power		
5	PD0-OSC_IN	I/O	RCC_OSC_IN	
6	PD1-OSC_OUT	I/O	RCC_OSC_OUT	
7	NRST	Reset		
12	VSSA	Power		
13	VDDA	Power		
18	VSS	Power		
19	VDD	Power		
31	VSS	Power		
32	VDD	Power		
36	PB15 *	I/O	GPIO_Output	LED3
37	PC6 *	I/O	GPIO_Output	LED2
38	PC7 *	I/O	GPIO_Output	LED1
42	PA9 *	I/O	GPIO_Output	
44	PA11	I/O	USB_OTG_FS_DM	
45	PA12	I/O	USB_OTG_FS_DP	
46	PA13	I/O	SYS_JTMS-SWDIO	
47	VSS	Power		
48	VDD	Power		
49	PA14	I/O	SYS_JTCK-SWCLK	
60	BOOT0	Boot		
63	VSS	Power		
64	VDD	Power		

\* The pin is affected with an I/O function

## 4. Clock Tree Configuration



## 5. Software Project

### 5.1. Project Settings

Name	Value
Project Name	stm32f105_1
Project Folder	C:\Project\stm32f105_1
Toolchain / IDE	SW4STM32
Firmware Package Name and Version	STM32Cube FW_F1 V1.8.0

### 5.2. Code Generation Settings

Name	Value
STM32Cube MCU packages and embedded software	Copy only the necessary library files
Generate peripheral initialization as a pair of '.c/.h' files	No
Backup previously generated files when re-generating	No
Delete previously generated files when not re-generated	Yes
Set all free pins as analog (to optimize the power consumption)	No

## 6. Power Consumption Calculator report

### 6.1. Microcontroller Selection

Series	STM32F1
Line	STM32F105/107
MCU	STM32F105RBTx
Datasheet	15274_Rev10

### 6.2. Parameter Selection

Temperature	25
Vdd	3.3

## 7. IPs and Middleware Configuration

### 7.1. RCC

#### High Speed Clock (HSE): Crystal/Ceramic Resonator

##### 7.1.1. Parameter Settings:

###### System Parameters:

VDD voltage (V)	3.3
Instruction Cache	Enabled
Prefetch Buffer	Enabled
Data Cache	Enabled
Flash Latency(WS)	2 WS (3 CPU cycle)

###### RCC Parameters:

HSI Calibration Value	16
HSE Startup Timeout Value (ms)	100
LSE Startup Timeout Value (ms)	5000

### 7.2. SYS

#### Debug: Serial Wire

#### Timebase Source: TIM1

### 7.3. USB\_OTG\_FS

#### Mode: Host\_Only

##### 7.3.1. Parameter Settings:

Speed	Host Full Speed 12MBit/s
Signal start of frame	Disabled

### 7.4. FATFS

#### mode: USB Disk

##### 7.4.1. Set Defines:

###### Version:

FATFS version	R0.11
---------------	-------

###### Function Parameters:

FS_READONLY (Read-only mode)	Disabled
------------------------------	----------

FS_MINIMIZE (Minimization level)	Disabled
USE_STRFUNC (String functions)	Enabled with LF -> CRLF conversion
USE_FIND (Find functions)	Disabled
USE_MKFS (Make filesystem function)	Enabled
USE_FASTSEEK (Fast seek function)	Enabled
USE_LABEL (Volume label functions)	Disabled
USE_FORWARD (Forward function)	Disabled
USE_BUFF_WO_ALIGNMENT (Data alignment management)	Enabled

#### Locale and Namespace Parameters:

CODE_PAGE (Code page on target)	Multilingual Latin 1 (OEM)
USE_LFN (Use Long Filename)	Disabled
MAX_LFN (Max Long Filename)	255
LFN_UNICODE (Enable Unicode)	ANSI/OEM
STRF_ENCODE (Character encoding)	UTF-8
FS_RPATH (Relative Path)	Disabled

#### Physical Drive Parameters:

VOLUMES (Logical drives)	1
MAX_SS (Maximum Sector Size)	<b>4096 *</b>
MIN_SS (Minimum Sector Size)	512
MULTI_PARTITION (Volume partitions feature)	Disabled
USE_TRIM (Erase feature)	Disabled
FS_NOFSINFO (Force full FAT scan)	0

#### System Parameters:

FS_TINY (Tiny mode)	Disabled
FS_NORTC (Timestamp feature)	Dynamic timestamp
NORTC_YEAR (Year for timestamp)	2015
NORTC_MON (Month for timestamp)	6
NORTC_MDAY (Day for timestamp)	4
WORD_ACCESS (Platform dependent access option)	Byte access
FS_REENTRANT (Re-Entrancy)	Disabled
FS_TIMEOUT (Timeout ticks)	1000
SYNC_t (O/S sync object)	osSemaphoreId
FS_LOCK (Number of files opened simultaneously)	2

### 7.4.2. Advanced Settings:

#### USBH:

USBH instance	USB Host MSC FS
---------------	-----------------



## 7.5. USB\_HOST

### Class for FS IP: Mass Storage Host Class

#### 7.5.1. Parameter Settings:

##### Host Configuration:

USBH_MAX_NUM_ENDPOINTS (Maximum number of endpoints)	2
USBH_MAX_NUM_INTERFACES (Maximum number of interfaces)	2
USBH_MAX_NUM_SUPPORTED_CLASS (Maximum number of supported class)	1
USBH_MAX_NUM_CONFIGURATION (Maximum number of supported configuration)	1
USBH_KEEP_CFG_DESCRIPTOR (Keep the configuration into RAM)	Enabled
USBH_MAX_SIZE_CONFIGURATION (Maximum size in bytes for the Configuration Descriptor)	256
USBH_MAX_DATA_BUFFER (Maximum size of temporary data)	512
USBH_DEBUG_LEVEL (USBH Debug Level)	0: No debug message

##### CMSIS\_RTOS:

USBH_USE_OS (Enable the support of an RTOS)	Disabled
---	----------

\* User modified value

## 8. System Configuration

### 8.1. GPIO configuration

IP	Pin	Signal	GPIO mode	GPIO pull/up pull down	Max Speed	User Label
RCC	PD0-OSC_IN	RCC_OSC_IN	n/a	n/a	n/a	
	PD1-OSC_OUT	RCC_OSC_OUT	n/a	n/a	n/a	
SYS	PA13	SYS_JTMS-SWDIO	n/a	n/a	n/a	
	PA14	SYS_JTCK-SWCLK	n/a	n/a	n/a	
USB_OTG_FS	PA11	USB_OTG_FS_DM	n/a	n/a	n/a	
	PA12	USB_OTG_FS_DP	n/a	n/a	n/a	
GPIO	PB15	GPIO_Output	Output Push Pull	No pull-up and no pull-down	Low	LED3
	PC6	GPIO_Output	Output Push Pull	No pull-up and no pull-down	Low	LED2
	PC7	GPIO_Output	Output Push Pull	No pull-up and no pull-down	Low	LED1
	PA9	GPIO_Output	Output Push Pull	No pull-up and no pull-down	Low	

### 8.2. DMA configuration

nothing configured in DMA service

### 8.3. NVIC configuration

Interrupt Table	Enable	Preenmption Priority	SubPriority
Non maskable interrupt	true	0	0
Hard fault interrupt	true	0	0
Memory management fault	true	0	0
Prefetch fault, memory access fault	true	0	0
Undefined instruction or illegal state	true	0	0
System service call via SWI instruction	true	0	0
Debug monitor	true	0	0
Pendable request for system service	true	0	0
System tick timer	true	0	0
TIM1 update interrupt	true	0	0
USB OTG FS global interrupt	true	0	0
PVD interrupt through EXTI line 16		unused	
Flash global interrupt		unused	
RCC global interrupt		unused	

\* User modified value

## **9. Software Pack Report**