

UM0391 User manual

DfuSe File Format Specification

Introduction

The Device Firmware Upgrade specification specifies the contents of a data structure to be placed at the end of the DFU files, but leaves the definition of the content up to the vendor. This document describes the format used with the DFU solution from STMicroelectronics.

Contents UM0391

Contents

1	Devi	ce Firm	ware Upgrade STMicroelectronics Extension 3	
2	DFU	File for	mat 4	
	2.1	DFU P	refix section	ļ
	2.2	DFU S	uffix section	ļ
	2.3	DFU In	nages section	:
		2.3.1	DFU Image5	;
		2.3.2	Target Prefix	:
		2.3.3	Image Element	:
3	Revi	sion his	tory	,

1 Device Firmware Upgrade STMicroelectronics Extension

The reason for creating this DFU extension is that the standard device firmware upgrade protocol is too specialized in terms of protocol versus the target or the application.

This extension makes it easy to use DFU with all 8 or 32-bit microcontrollers, simply letting the PC side know the target memory mapping. In addition, the DFU file format has been updated, to be able to build DFU files from standard 8 or 32-bit s19, hex or bin formats. The result is a new revision of the standard DFU revision 1.1, called DfuSe for Device firmware upgrade STMicroelectronics Extension.


57

DFU File format UM0391

2 DFU File format

The basic DFU file format to be used with STMicroelectronics DFU solution is based on three sections; Prefix, Images and Suffix, described as follows:

Figure 1. DFU File general format



2.1 DFU Prefix section

The DFU prefix placed as a header file is the first part read by the software application, used to retrieve the file context, and enable valid DFU files to be recognized. The Prefix buffer is represented in Big Endian order.

The prefix packet is structured as follows:

Figure 2. DFUPREFIX

0	1	2	3	4	5	6	7	8	9	10
	s	zSignatuı "DfuSe"	re		bVersion (0x01)		DFUIma	ageSize		bTargets

- The szSignature field, five-byte coded, presents the file identifier that enables valid DFU files to be recognized, and incompatible changes detected. This identifier should be updated when major changes are made to the file format. This field is set to "DfuSe".
- The bVersion field, one-byte coded, presents the DFU format revision, The value will be incremented if extra fields are added to one of the three sections. Software exploring the file can either treat the file depending on its specified revision, or just test for valid value.
- The DFUImageSize field, four-byte coded, presents the total DFU file length in bytes.
- the bTargets field, one-byte coded, presents the number of DFU image stored in the file.

2.2 DFU Suffix section

The DFU Suffix, as specified in the DFU specification, allows the host software to detect and prevent attempts to download incompatible firmware. The Suffix buffer is represented in Little Endian order.

The Suffix packet is structured as follows:

UM0391 DFU File format

rigule 3. Dru Sulli	Figure	3.	DFU	Suffix
---------------------	---------------	----	-----	--------

0	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
bcdDeviceLo	bcdDeviceHi	idProductLo	idProductHi	idVendorLo	idVendorHi	bcdDFULo (0x1A)	\sim	ucDf	uSigna (UFD)	ature	bLength (16)		dwC	CRC	

- The bcdDevice field gives the firmware version contained in the file, or 0xFFFF if ignored.
- The idProduct and idVendor field give the Product ID and Vendor ID respectively of the device that the file is intended for, or 0xFFFF if the field is ignored.
- The bcdDFU field, fixed to 0x011A, gives the DFU specification number. This value differs from that specified in standard DFU rev1.1.
- The ucSignature field contains a fixed string of three unsigned characters (44h, 46h, 55h). In the file they appear in reverse order, allowing valid DFU files to be recognized.
- The bLength field, currently fixed to 16, gives the length of the DFU Suffix itself in bytes.
- The dwCRC (Cyclic Redundancy Check) field is the CRC calculated over the whole file except for the dwCRC data itself.

2.3 DFU Images section

The images section placed between the prefix and suffix as a body of the DFU file, contains a list of DFU images indexed by the alternate setting.

Figure 4. DFU Images*

DFU Image 1
DFU Image2
DFU Image N-1
DFU Image N

2.3.1 DFU Image

The DFU Image contains the effective data of the firmware, starting by a Target prefix record followed by a number of Image elements.

Figure 5. DFU Image

Target Prefix	
Image Element 1	
ImageElement 2	
:	_

DFU File format UM0391

Figure 5. DFU Image

ImageElement N-1
ImageElement N

2.3.2 Target Prefix

The target prefix record is used to describe the associated image. The Target Prefix buffer is represented in Big Endian order.

Figure 6. Target Prefix

0	6	7	11	266	270 273
szSignature "Target"	bAlternateSetting	bTargetNamed	szTargetName	dwTargetSize	dwNbElements

- The szSignature field, 6-byte coded, fixed to "Target".
- The bAlternateSetting field gives the device alternate setting for which the associated image can be used.
- The bTargetNamed field is a boolean value which indicates if the target is named or not.
- The szTargetName field gives the target name.
- The dwTargetSize field gives the whole length of the associated image excluding the Target prefix.
- The dwNbElements field gives the number of elements in the associated image.

2.3.3 Image Element

The Image element structured as follows, provides a data record containing the effective firmware data preceded by the data address and data size. The Image Element buffer is represented in Big Endian order.

Figure 7. Image Element

0	1	2	3	4	5	6	7	8
dw	dwElementAddress dwElementSize					9	Data	

- The dwElementAddress field gives the 4-byte starting address of the data.
- The dwElementSize field gives the size of the contained data.
- The Data field present the effective data.

UM0391 Revision history

3 Revision history

Table 1. Document revision history

Date	Revision	Changes
15-Feb-2007	1	Initial release.

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2007 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

577