

STM32 CubeMX

1. Description

1.1. Project

Project Name	LWIP_FreeRTOS
Board Name	custom
Generated with:	STM32CubeMX 6.10.0
Date	02/23/2024


1.2. MCU

MCU Series	STM32F7
MCU Line	STM32F7x6
MCU name	STM32F746NGHx
MCU Package	TFBGA216
MCU Pin number	216

1.3. Core(s) information

Core(s)	Arm Cortex-M7
---------	---------------

2. Pinout Configuration




TFPGA216 (Top view)

3. Pins Configuration

Pin Number TFBGA216	Pin Name (function after reset)	Pin Type	Alternate Function(s)	Label
A4	PG14	I/O	ETH_TXD1	
B3	PG13	I/O	ETH_TXD0	
B8	PG11	I/O	ETH_TX_EN	
C1	VBAT	Power		
E5	PDR_ON	Reset		
E6	BOOT0	Boot		
E7	VDD	Power		
E8	VDD	Power		
E9	VDD	Power		
E10	VDD	Power		
E11	VCAP_2	Power		
F2	VSS	Power		
F4	VDD	Power		
F5	VDD	Power		
F6	VSS	Power		
F7	VSS	Power		
F8	VSS	Power		
F9	VSS	Power		
F10	VSS	Power		
F11	VDD	Power		
G5	VDD	Power		
G6	VSS	Power		
G10	VSS	Power		
G11	VDDUSB	Power		
H5	VDD	Power		
H6	VSS	Power		
H10	VSS	Power		
H11	VDD	Power		
J1	NRST	Reset		
J5	VDD	Power		
J6	VSS	Power		
J10	VSS	Power		
J11	VDD	Power		
K1	PF7	I/O	UART7_TX	
K2	PF6	I/O	UART7_RX	
K5	VDD	Power		

Pin Number TFBGA216	Pin Name (function after reset)	Pin Type	Alternate Function(s)	Label
K6	VSS	Power		
K7	VSS	Power		
K8	VSS	Power		
K9	VSS	Power		
K10	VSS	Power		
K11	VDD	Power		
L5	BYPASS_REG	Reset		
L6	VSS	Power		
L7	VDD	Power		
L8	VDD	Power		
L9	VDD	Power		
L10	VDD	Power		
L11	VCAP_1	Power		
M1	VSSA	Power		
M3	PC1	I/O	ETH_MDC	
N1	VREF-	Power		
N2	PA1	I/O	ETH_REF_CLK	
N5	PC4	I/O	ETH_RXD0	
P1	VREF+	Power		
P2	PA2	I/O	ETH_MDIO	
P5	PC5	I/O	ETH_RXD1	
R1	VDDA	Power		
R3	PA7	I/O	ETH_CRSDV	

4. Clock Tree Configuration



5. Software Project

5.1. Project Settings

Name	Value
Project Name	LWIP_FreeRTOS
Project Folder	C:\Projects\STM32_Projects\LWIP_FreeRTOS
Toolchain / IDE	STM32CubeIDE
Firmware Package Name and Version	STM32Cube FW_F7 V1.17.1
Application Structure	Advanced
Generate Under Root	Yes
Do not generate the main()	No
Minimum Heap Size	0x200
Minimum Stack Size	0x400

5.2. Code Generation Settings

Name	Value
STM32Cube MCU packages and embedded software	Copy only the necessary library files
Generate peripheral initialization as a pair of '.c/.h' files	No
Backup previously generated files when re-generating	No
Keep User Code when re-generating	Yes
Delete previously generated files when not re-generated	Yes
Set all free pins as analog (to optimize the power consumption)	No
Enable Full Assert	No

5.3. Advanced Settings - Generated Function Calls

Rank	Function Name	Peripheral Instance Name
1	SystemClock_Config	RCC
2	MX_GPIO_Init	GPIO
3	MX_LWIP_Init	LWIP
4	MX_UART7_Init	UART7

1. Power Consumption Calculator report

1.1. Microcontroller Selection

Series	STM32F7
Line	STM32F7x6
MCU	STM32F746NGHx
Datasheet	DS10916_Rev4

1.2. Parameter Selection

Temperature	25
Vdd	3.3

1.3. Battery Selection

Battery	Alkaline(9V)
Capacity	625.0 mAh
Self Discharge	0.3 %/month
Nominal Voltage	9.0 V
Max Cont Current	200.0 mA
Max Pulse Current	0.0 mA
Cells in series	1
Cells in parallel	1


1.4. Sequence

Step	Step1	Step2
Mode	RUN	STOP UDM (Under Drive)
Vdd	3.3	3.3
Voltage Source	Battery	Battery
Range	Scale1-High	No Scale
Fetch Type	ITCM/FLASH/REGON	n/a
CPU Frequency	216 MHz	0 Hz
Clock Configuration	HSE PLL	Regulator LP Flash-PwrDwn
Clock Source Frequency	4 MHz	0 Hz
Peripherals		
Additional Cons.	0 mA	0 mA
Average Current	130 mA	100 μ A
Duration	0.1 ms	0.9 ms
DMIPS	462.0	0.0
Ta Max	92.56	104.99
Category	In DS Table	In DS Table

1.5. Results

Sequence Time	1 ms	Average Current	13.09 mA
Battery Life	1 day, 23 hours	Average DMIPS	462.24005 DMIPS

1.6. Chart



2. Peripherals and Middlewares Configuration

2.1. CORTEX_M7

2.1.1. Parameter Settings:

Speculation default mode Settings:

Speculation default mode Disabled

Cortex Interface Settings:

Flash Interface AXI Interface

ART ACCELERATOR Disabled

Instruction Prefetch **Enabled ***

CPU ICache **Enabled ***

CPU DCache **Enabled ***

Cortex Memory Protection Unit Control Settings:

MPU Control Mode **Background Region Privileged accesses only + MPU Disabled during hard fault, NMI and FAULTMASK handlers ***

Cortex Memory Protection Unit Region 0 Settings:

MPU Region **Enabled ***

MPU Region Base Address **0x2004c000 ***

MPU Region Size **32KB ***

MPU SubRegion Disable **0x0 ***

MPU TEX field level **level 1 ***

MPU Access Permission **ALL ACCESS PERMITTED ***

MPU Instruction Access **DISABLE ***

MPU Shareability Permission **ENABLE ***

MPU Cacheable Permission DISABLE

MPU Bufferable Permission DISABLE

Cortex Memory Protection Unit Region 1 Settings:

MPU Region Disabled

Cortex Memory Protection Unit Region 2 Settings:

MPU Region Disabled

Cortex Memory Protection Unit Region 3 Settings:

MPU Region Disabled

Cortex Memory Protection Unit Region 4 Settings:

MPU Region Disabled

Cortex Memory Protection Unit Region 5 Settings:

MPU Region Disabled

Cortex Memory Protection Unit Region 6 Settings:

MPU Region Disabled

Cortex Memory Protection Unit Region 7 Settings:

MPU Region Disabled

2.2. ETH

Mode: RMII

2.2.1. Parameter Settings:

General : Ethernet Configuration:

Warning	The ETH can work only when RAM is pointing at 0x24000000
Note	PHY Driver must be configured from the LwIP 'Platform Settings' top right tab
Ethernet MAC Address	00:80:E1:00:00:00
Tx Descriptor Length	4
First Tx Descriptor Address	0x2004c0a0 *
Rx Descriptor Length	4
First Rx Descriptor Address	0x2004c000 *
Rx Buffers Length	1536
Rx Mode	Interrupt Mode

2.3. RCC

2.3.1. Parameter Settings:

System Parameters:

VDD voltage (V)	3.3
Flash Latency(WS)	7 WS (8 CPU cycle)

RCC Parameters:

HSI Calibration Value	16
TIM Prescaler Selection	Disabled
HSE Startup Timeout Value (ms)	100
LSE Startup Timeout Value (ms)	5000

Power Parameters:

Power Over Drive	Enabled
Power Regulator Voltage Scale	Power Regulator Voltage Scale 1

2.4. SYS

Timebase Source: TIM3

2.5. UART7

Mode: Asynchronous

2.5.1. Parameter Settings:

Basic Parameters:

Baud Rate	115200
Word Length	8 Bits (including Parity)
Parity	None
Stop Bits	1

Advanced Parameters:

Data Direction	Receive and Transmit
Over Sampling	16 Samples
Single Sample	Disable

Advanced Features:

Auto Baudrate	Disable
TX Pin Active Level Inversion	Disable
RX Pin Active Level Inversion	Disable
Data Inversion	Disable
TX and RX Pins Swapping	Disable
Overrun	Enable
DMA on RX Error	Enable
MSB First	Disable

2.6. FREERTOS

Interface: CMSIS_V1

2.6.1. Config parameters:

API:

FreeRTOS API	CMSIS v1
--------------	----------

Versions:

FreeRTOS version	10.2.1
CMSIS-RTOS version	1.02

MPU/FPU:

ENABLE_MPU	Disabled
ENABLE_FPU	Disabled

Kernel settings:

USE_PREEMPTION	Enabled
CPU_CLOCK_HZ	SystemCoreClock
TICK_RATE_HZ	1000
MAX_PRIORITIES	7
MINIMAL_STACK_SIZE	512 *
MAX_TASK_NAME_LEN	16
USE_16_BIT_TICKS	Disabled
IDLE_SHOULD_YIELD	Enabled
USE_MUTEXES	Enabled
USE_RECURSIVE_MUTEXES	Disabled
USE_COUNTING_SEMAPHORES	Disabled
QUEUE_REGISTRY_SIZE	8
USE_APPLICATION_TASK_TAG	Disabled
ENABLE_BACKWARD_COMPATIBILITY	Enabled
USE_PORT_OPTIMISED_TASK_SELECTION	Enabled
USE_TICKLESS_IDLE	Disabled
USE_TASK_NOTIFICATIONS	Enabled
RECORD_STACK_HIGH_ADDRESS	Disabled

Memory management settings:

Memory Allocation	Dynamic / Static
TOTAL_HEAP_SIZE	15360
Memory Management scheme	heap_4

Hook function related definitions:

USE_IDLE_HOOK	Disabled
USE_TICK_HOOK	Disabled
USE_MALLOC_FAILED_HOOK	Disabled
USE_DAEMON_TASK_STARTUP_HOOK	Disabled
CHECK_FOR_STACK_OVERFLOW	Disabled

Run time and task stats gathering related definitions:

GENERATE_RUN_TIME_STATS	Disabled
USE_TRACE_FACILITY	Disabled
USE_STATS_FORMATTING_FUNCTIONS	Disabled

Co-routine related definitions:

USE_CO_ROUTINES	Disabled
MAX_CO_ROUTINE_PRIORITIES	2

Software timer definitions:

USE_TIMERS	Disabled
------------	----------

Interrupt nesting behaviour configuration:

LIBRARY_LOWEST_INTERRUPT_PRIORITY	15
LIBRARY_MAX_SYSCALL_INTERRUPT_PRIORITY	5

Added with 10.2.1 support:

MESSAGE_BUFFER_LENGTH_TYPE	size_t
USE_POSIX_ERRNO	Disabled

2.6.2. Include parameters:

Include definitions:

vTaskPrioritySet	Enabled
uxTaskPriorityGet	Enabled
vTaskDelete	Enabled
vTaskCleanUpResources	Disabled
vTaskSuspend	Enabled
vTaskDelayUntil	Disabled
vTaskDelay	Enabled
xTaskGetSchedulerState	Enabled
xTaskResumeFromISR	Enabled
xQueueGetMutexHolder	Disabled
xSemaphoreGetMutexHolder	Disabled
pcTaskGetTaskName	Disabled
uxTaskGetStackHighWaterMark	Disabled
xTaskGetCurrentTaskHandle	Disabled
eTaskGetState	Disabled
xEventGroupSetBitFromISR	Disabled
xTimerPendFunctionCall	Disabled
xTaskAbortDelay	Disabled
xTaskGetHandle	Disabled
uxTaskGetStackHighWaterMark2	Disabled

2.6.3. Advanced settings:

Newlib settings (see parameter description first):

USE_NEWLIB_REENTRANT	Enabled *
----------------------	------------------

Project settings (see parameter description first):

Use FW pack heap file	Enabled
-----------------------	---------

2.7. LWIP

mode: Enabled

Advanced parameters are not listed except if modified by user.

2.7.1. General Settings:

LwIP Version:

LWIP Version (Version of LwIP supported by CubeMX ** CubeMX specific **) 2.1.2

IPv4 - DHCP Options:

LWIP_DHCP (DHCP Module) Enabled

RTOS Dependency:

WITH_RTOS (Use FREERTOS ** CubeMX specific **) Enabled

CMSIS_VERSION (CMSIS API Version used) CMSIS v1

RTOS_USE_NEWLIB_REENTRANT (RTOS used - 1) Enabled

Platform Settings:

PHY Driver Choose/LAN8742/DP83848

Protocols Options:

LWIP_ICMP (ICMP Module Activation) Enabled

LWIP_IGMP (IGMP Module) Disabled

LWIP_DNS (DNS Module) Disabled

LWIP_UDP (UDP Module) Enabled

MEMP_NUM_UDP_PCB (Number of UDP Connections) 4

LWIP_TCP (TCP Module) Enabled

MEMP_NUM_TCP_PCB (Number of TCP Connections) 5

2.7.2. Key Options:

Infrastructure - OS Awareness Option:

NO_SYS (OS Awareness) OS Used

Infrastructure - Timers Options:

LWIP_TIMERS (Use Support For sys_timeout) Enabled

Infrastructure - Core Locking and MPU Options:

SYS_LIGHTWEIGHT_PROT (Memory Functions Protection) Enabled

Infrastructure - Heap and Memory Pools Options:

MEM_SIZE (Heap Memory Size) **10*1024 ***

Infrastructure - Internal Memory Pool Sizes:

MEMP_NUM_PBUF (Number of Memory Pool struct Pbufs) 16

MEMP_NUM_RAW_PCB (Number of Raw Protocol Control Blocks) 4

MEMP_NUM_TCP_PCB_LISTEN (Number of Listening TCP Connections) 8

MEMP_NUM_TCP_SEG (Number of TCP Segments simultaneously queued) 16

MEMP_NUM_LOCALHOSTLIST (Number of Host Entries in the Local Host List) 1

Pbuf Options:

PBUF_POOL_SIZE (Number of Buffers in the Pbuf Pool) 16

PBUF_POOL_BUFSIZE (Size of each pbuf in the pbuf pool) 592

IPv4 - ARP Options:

LWIP_ARP (ARP Functionality) Enabled

Callback - TCP Options:

TCP_TTL (Number of Time-To-Live Used by TCP Packets) 255
 TCP_WND (TCP Receive Window Maximum Size) 2144
 TCP_QUEUE_OOSEQ (Allow Out-Of-Order Incoming Packets) Enabled
 LWIP_TCP_SACK_OUT (Allow Sending Selective Acknowledgements) Disabled
 TCP_MSS (Maximum Segment Size) 536
 TCP_SND_BUF (TCP Sender Buffer Space) 1072
 TCP_SND_QUEUELEN (Number of Packet Buffers Allowed for TCP Sender) 9

Network Interfaces Options:

LWIP_NETIF_STATUS_CALLBACK (Callback Function on Interface Status Changes) Disabled
 LWIP_NETIF_EXT_STATUS_CALLBACK (Extended Callback Function for several netif) Disabled
 LWIP_NETIF_LINK_CALLBACK (Callback Function on Interface Link Changes) Enabled

NETIF - Loopback Interface Options:

LWIP_NETIF_LOOPBACK (NETIF Loopback) Disabled

Infrastructure - Threading Options:

TCPIP_THREAD_NAME (TCPIP Thread Name) "tcpip_thread"
 TCPIP_THREAD_STACKSIZE (TCPIP Thread Stack Size) 1024
 TCPIP_THREAD_PRIO (TCPIP Thread Priority Level) 3
 TCPIP_MBOX_SIZE (TCPIP Mailbox Size) 6
 DEFAULT_THREAD_NAME (Default LwIP Thread Name) "lwIP"
 DEFAULT_THREAD_STACKSIZE (Default LwIP Thread Stack Size) 1024
 DEFAULT_THREAD_PRIO (Default LwIP Thread Priority Level) 3
 DEFAULT_RAW_RECVMBOX_SIZE (Default Mailbox Size on a NETCONN Raw) 0
 DEFAULT_TCP_RECVMBOX_SIZE (Default Mailbox Size on a NETCONN TCP) 6
 DEFAULT_ACCEPTMBOX_SIZE (Default Mailbox Size for Incoming Connections) 6

Thread Safe APIs - Netconn Options:

LWIP_NETCONN (NETCONN API) Enabled

Thread Safe APIs - Socket Options:

LWIP_SOCKET (Socket API) Enabled
 LWIP_COMPAT_SOCKETS (BSD-style Socket Functions Names) 1
 LWIP_SOCKET_OFFSET (Socket Offset Number) 0
 LWIP_SOCKET_SELECT (Select for Socket) Enabled
 LWIP_SOCKET_POLL (Poll for Socket) Enabled

2.7.3. PPP:

PPP Options:

PPP_SUPPORT (PPP Module) Disabled

2.7.4. IPv6:

IPv6 Options:

LWIP_IPV6 (IPv6 Protocol) Disabled

2.7.5. HTTPD:

HTTPD Options:

LWIP_HTTPD (LwIP HTTPD Support ** CubeMX specific **) Disabled

2.7.6. SNMP:

SNMP Options:

LWIP_SNMP (LwIP SNMP Agent) Disabled

2.7.7. SNTP/SMTP:

SNTP Options:

LWIP_SNTP (LWIP SNTP Support ** CubeMX specific **) Disabled

SMTP Options:

LWIP_SMTP (LWIP SMTP Support ** CubeMX specific **) Disabled

2.7.8. MDNS/TFTP:

MDNS Options:

LWIP_MDNS (Multicast DNS Support ** CubeMX specific **) Disabled

TFTP Options:

LWIP_TFTP (TFTP Support ** CubeMX specific **) Disabled

2.7.9. Perf/Checks:

Sanity Checks:

LWIP_DISABLE_TCP_SANITY_CHECKS (TCP Sanity Checks) Disabled

LWIP_DISABLE_MEMP_SANITY_CHECKS (MEMP Sanity Checks) Disabled

Performance Options:

LWIP_PERF (Performance Testing for LwIP) Disabled

2.7.10. Statistics:

Debug - Statistics Options:

LWIP_STATS (Statistics Collection) Disabled

2.7.11. Checksum:

Infrastructure - Checksum Options:

CHECKSUM_BY_HARDWARE (Hardware Checksum ** CubeMX specific **)	Enabled
LWIP_CHECKSUM_CTRL_PER_NETIF (Generate/Check Checksum per Netif)	Disabled
CHECKSUM_GEN_IP (Generate Software Checksum for Outgoing IP Packets)	Disabled
CHECKSUM_GEN_UDP (Generate Software Checksum for Outgoing UDP Packets)	Disabled
CHECKSUM_GEN_TCP (Generate Software Checksum for Outgoing TCP Packets)	Disabled
CHECKSUM_GEN_ICMP (Generate Software Checksum for Outgoing ICMP Packets)	Disabled
CHECKSUM_GEN_ICMP6 (Generate Software Checksum for Outgoing ICMP6 Packets)	Disabled
CHECKSUM_CHECK_IP (Generate Software Checksum for Incoming IP Packets)	Disabled
CHECKSUM_CHECK_UDP (Generate Software Checksum for Incoming UDP Packets)	Disabled
CHECKSUM_CHECK_TCP (Generate Software Checksum for Incoming TCP Packets)	Disabled
CHECKSUM_CHECK_ICMP (Generate Software Checksum for Incoming ICMP Packets)	Disabled
CHECKSUM_CHECK_ICMP6 (Generate Software Checksum for Incoming ICMP6 Packets)	Disabled

2.7.12. Debug:

LwIP Main Debugging Options:

LWIP_DBG_MIN_LEVEL (Minimum Level) All

2.7.13. Platform Settings:

Driver_PHY LAN8742

* User modified value

3. System Configuration

3.1. GPIO configuration

IP	Pin	Signal	GPIO mode	GPIO pull/up pull down	Max Speed	User Label
ETH	PG14	ETH_TXD1	Alternate Function Push Pull	No pull-up and no pull-down	Very High *	
	PG13	ETH_TXD0	Alternate Function Push Pull	No pull-up and no pull-down	Very High *	
	PG11	ETH_TX_EN	Alternate Function Push Pull	No pull-up and no pull-down	Very High *	
	PC1	ETH_MDC	Alternate Function Push Pull	No pull-up and no pull-down	Very High *	
	PA1	ETH_REF_CLK	Alternate Function Push Pull	No pull-up and no pull-down	Very High *	
	PC4	ETH_RXD0	Alternate Function Push Pull	No pull-up and no pull-down	Very High *	
	PA2	ETH_MDIO	Alternate Function Push Pull	No pull-up and no pull-down	Very High *	
	PC5	ETH_RXD1	Alternate Function Push Pull	No pull-up and no pull-down	Very High *	
	PA7	ETH_CRSDV	Alternate Function Push Pull	No pull-up and no pull-down	Very High *	
UART7	PF7	UART7_TX	Alternate Function Push Pull	No pull-up and no pull-down	Very High *	
	PF6	UART7_RX	Alternate Function Push Pull	No pull-up and no pull-down	Very High *	

3.2. DMA configuration

nothing configured in DMA service

3.3. NVIC configuration

3.3.1. NVIC

Interrupt Table	Enable	Preenmption Priority	SubPriority
Non maskable interrupt	true	0	0
Hard fault interrupt	true	0	0
Memory management fault	true	0	0
Pre-fetch fault, memory access fault	true	0	0
Undefined instruction or illegal state	true	0	0
System service call via SWI instruction	true	0	0
Debug monitor	true	0	0
Pendable request for system service	true	15	0
System tick timer	true	15	0
TIM3 global interrupt	true	15	0
Ethernet global interrupt	true	5	0
PVD interrupt through EXTI line 16		unused	
Flash global interrupt		unused	
RCC global interrupt		unused	
Ethernet wake-up interrupt through EXTI line 19		unused	
FPU global interrupt		unused	
UART7 global interrupt		unused	

3.3.2. NVIC Code generation

Enabled interrupt Table	Select for init sequence ordering	Generate IRQ handler	Call HAL handler
Non maskable interrupt	false	true	false
Hard fault interrupt	false	true	false
Memory management fault	false	true	false
Pre-fetch fault, memory access fault	false	true	false
Undefined instruction or illegal state	false	true	false
System service call via SWI instruction	false	false	false
Debug monitor	false	true	false
Pendable request for system service	false	false	false
System tick timer	false	false	true
TIM3 global interrupt	false	true	true
Ethernet global interrupt	false	true	true

* User modified value

4. System Views

4.1. Category view

4.1.1. Current

Middleware

FREERTOS



LWIP



System Core

Analog

Timers

Connectivity

Multimedia

Security

Computing

CORTEX_M7



ETH



DMA

UART7



GPIO



NVIC



RCC



SYS



5. Docs & Resources

Type	Link
BSDL files	https://www.st.com/resource/en/bsdl_model/stm32f7_bsd.zip
IBIS models	https://www.st.com/resource/en/ibis_model/stm32f7_ibis.zip
System View Description	https://www.st.com/resource/en/svd/stm32f7-svd.zip
Presentations	https://www.st.com/resource/en/product_presentation/stm32-stm8_embedded_software_solutions.pdf
Presentations	https://www.st.com/resource/en/product_presentation/stm32_eval_tools_portfolio.pdf
Presentations	https://www.st.com/resource/en/product_presentation/stm32_stm8_functional-safety-packages.pdf
Presentations	https://www.st.com/resource/en/product_presentation/stm32-stm8_software_development_tools.pdf
Presentations	https://www.st.com/resource/en/product_presentation/microcontrollers-stm32-family-overview.pdf
Brochures	https://www.st.com/resource/en/brochure/brstm32f7.pdf
Brochures	https://www.st.com/resource/en/brochure/products-and-solutions-for-plcs-and-smart-i-os.pdf
Flyers	https://www.st.com/resource/en/flyer/flstm32nucleo.pdf
Flyers	https://www.st.com/resource/en/flyer/flstmcsuite.pdf
Flyers	https://www.st.com/resource/en/flyer/flstm32trust.pdf
Flyers	https://www.st.com/resource/en/flyer/flstm32gui.pdf
Application Notes	https://www.st.com/resource/en/application_note/an1181-electrostatic-discharge-sensitivity-measurement-stmicroelectronics.pdf
Application Notes	https://www.st.com/resource/en/application_note/an1709-emc-design-guide-for-stm8-stm32-and-legacy-mcus-stmicroelectronics.pdf
Application Notes	https://www.st.com/resource/en/application_note/an2606-stm32-microcontroller-system-memory-boot-mode-stmicroelectronics.pdf
Application Notes	https://www.st.com/resource/en/application_note/an2639-soldering-recommendations-and-package-information-for-leadfree-ecopack-mcus

and-mpus-stmicroelectronics.pdf

- Application Notes https://www.st.com/resource/en/application_note/an2867-oscillator-design-guide-for-stm8afals-stm32-mcus-and-mpus-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an3126-audio-and-waveform-generation-using-the-dac-in-stm32-products-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an3154-can-protocol-used-in-the-stm32-bootloader-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an3155-usart-protocol-used-in-the-stm32-bootloader-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an3156-usb-dfu-protocol-used-in-the-stm32-bootloader-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4013-stm32-crossseries-timer-overview-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4031-using-the-stm32f2-stm32f4-and-stm32f7-series-dma-controller-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4221-i2c-protocol-used-in-the-stm32-bootloader-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4229-how-to-implement-a-vocoder-solution-using-stm32-microcontrollers-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4277-using-stm32-device-pwm-shutdown-features-for-motor-control-and-digital-power-conversion-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4286-spi-protocol-used-in-the-stm32-bootloader-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4566-extending-the-dac-performance-of-stm32-microcontrollers-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4655-virtually-increasing-the-number-of-serial-communication-peripherals-in-stm32-applications-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4660-migration-of-

microcontroller-applications-from-stm32f42xxx43xxx-devices-to-stm32f7-series-devices-stmicroelectronics.pdf

- Application Notes https://www.st.com/resource/en/application_note/an4661-getting-started-with-stm32f7-series-mcu-hardware-development-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4676-stm32f7-series-peripheral-interconnections-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4731-stm32cube-mcu-package-examples-for-stm32f7-series-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4750-handling-of-soft-errors-in-stm32-applications-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4759-using-the-hardware-realtime-clock-rtc-and-the-tamper-management-unit-tamp-with-stm32-microcontrollers-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4776-generalpurpose-timer-cookbook-for-stm32-microcontrollers-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4803-highspeed-si-simulations-using-ibis-and-boardlevel-simulations-using-hyperlynx-si-on-stm32-mcus-and-mpus-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4839-level-1-cache-on-stm32f7-series-and-stm32h7-series-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4850-stm32-mcus-spreadspectrum-clock-generation-principles-properties-and-implementation-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4861-lcdtft-display-controller-ltcd-on-stm32-mcus-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4908-stm32-usart-automatic-baud-rate-detection-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4936-migration-of-microcontroller-applications-from-stm32f7-series-to-stm32h743753-line-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4946-migration-of-microcontroller-applications-between-stm32f72xxx73xxx-and-stm32f74xxx75xxx-microcontrollers-stmicroelectronics.pdf

- Application Notes https://www.st.com/resource/en/application_note/an4989-stm32-microcontroller-debug-toolbox-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an5020-digital-camera-interface-dcml-on-stm32-mcus-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an5027-interfacing-pdm-digital-microphones-using-stm32-mcus-and-mpus-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an5036-thermal-management-guidelines-for-stm32-applications-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an5073-receiving-spdif-audio-stream-with-the-stm32f4f7h7-series-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an5543-enhanced-methods-to-handle-spi-communication-on-stm32-devices-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4760-quadspi-interface-on-stm32-microcontrollers-and-microprocessors--stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4899-stm32-microcontroller-gpio-hardware-settings-and-lowpower-consumption-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an5612-esd-protection-of-stm32-mcus-and-mpus-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an5293-migration-guide-from-stm32f7-series-to-stmh74x75x-stm32h72x73x-and-stmh7a37bx-devices-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an5156-introduction-to-stm32-microcontrollers-security-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4838-introduction-to-memory-protection-unit-management-on-stm32-mcus-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4230-random-number-generation-validation-using-nist-statistical-test-suite-for-stm32-microcontrollers-stmicroelectronics.pdf
- Application Notes https://www.st.com/resource/en/application_note/an4879-introduction-to

usb-hardware-and-pcb-guidelines-using-stm32-mcus-stmicroelectronics.pdf

Application Notes https://www.st.com/resource/en/application_note/an5225-introduction-to-usb-typec-power-delivery-for-stm32-mcus-and-mpus-stmicroelectronics.pdf

Application Notes https://www.st.com/resource/en/application_note/an2834-how-to-optimize-the-adc-accuracy-in-the-stm32-mcus-stmicroelectronics.pdf

Application Notes https://www.st.com/resource/en/application_note/an5816-how-to-build-stm32-lpbam-application-using-stm32cubemx-stmicroelectronics.pdf

Application Notes https://www.st.com/resource/en/application_note/an5537-how-to-use-adc-oversampling-techniques-to-improve-signal-to-noise-ratio-on-stm32-mcus-stmicroelectronics.pdf

Application Notes https://www.st.com/resource/en/application_note/an1202_freertos_guide-for-related-tools-freertos-guide-stmicroelectronics.pdf
& Software

Application Notes https://www.st.com/resource/en/application_note/an1602_semihosting_in_for-related-tools-_truestudio-how-to-do-semihosting-in-truestudio-stmicroelectronics.pdf
& Software

Application Notes https://www.st.com/resource/en/application_note/an1801_stm32cubeprog_for-related-tools-rammer_in_truestudio-installing-stm32cubeprogrammer-in-truestudio-stmicroelectronics.pdf
& Software

Application Notes https://www.st.com/resource/en/application_note/atollic_editing_keyboard_for-related-tools-_shortcuts-atollic-editing-keyboard-shortcuts-stmicroelectronics.pdf
& Software

Application Notes https://www.st.com/resource/en/application_note/iar_to_atollic_truestudio_for-related-tools-_migration_guide-truestudio-for-arm-migration-guide-iar-embedded-workbench-to-truestudio-stmicroelectronics.pdf
& Software

Application Notes https://www.st.com/resource/en/application_note/stm32cubemx_installation_in_truestudio-stm32cubemx-installation-in-truestudio-stmicroelectronics.pdf
& Software

Application Notes https://www.st.com/resource/en/application_note/an4044-floating-point-unit-demonstration-on-stm32-microcontrollers-stmicroelectronics.pdf
& Software

Application Notes https://www.st.com/resource/en/application_note/an4323-getting-started-

for related Tools & Software [with-stemwin-library-stmicroelectronics.pdf](#)

Application Notes for related Tools & Software https://www.st.com/resource/en/application_note/an4435-guidelines-for-obtaining-ulcsaiec-607301603351-class-b-certification-in-any-stm32-application-stmicroelectronics.pdf

Application Notes for related Tools & Software https://www.st.com/resource/en/application_note/an4657-stm32-inapplication-programming-iap-using-the-usart-stmicroelectronics.pdf

Application Notes for related Tools & Software https://www.st.com/resource/en/application_note/an4667-stm32f7-series-system-architecture-and-performance-stmicroelectronics.pdf

Application Notes for related Tools & Software https://www.st.com/resource/en/application_note/an4731-stm32cube-mcu-package-examples-for-stm32f7-series-stmicroelectronics.pdf

Application Notes for related Tools & Software https://www.st.com/resource/en/application_note/an4749-managing-lowpower-consumption-on-stm32f7-series-microcontrollers-stmicroelectronics.pdf

Application Notes for related Tools & Software https://www.st.com/resource/en/application_note/an4759-using-the-hardware-realtime-clock-rtc-and-the-tamper-management-unit-tamp-with-stm32-microcontrollers-stmicroelectronics.pdf

Application Notes for related Tools & Software https://www.st.com/resource/en/application_note/an4841-digital-signal-processing-for-stm32-microcontrollers-using-cmsis-stmicroelectronics.pdf

Application Notes for related Tools & Software https://www.st.com/resource/en/application_note/an5054-secure-programming-using-stm32cube programmer-stmicroelectronics.pdf

Application Notes for related Tools & Software https://www.st.com/resource/en/application_note/an5056-integration-guide-for-the-xcubesbsfu-stm32cube-expansion-package-stmicroelectronics.pdf

Application Notes for related Tools & Software https://www.st.com/resource/en/application_note/an5360-getting-started-with-projects-based-on-the-stm32mp1-series-in-stm32cubeide-stmicroelectronics.pdf

Application Notes for related Tools https://www.st.com/resource/en/application_note/an5361-getting-started-with-projects-based-on-dualcore-stm32h7-microcontrollers-in-

& Software	stm32cubeide-stmicroelectronics.pdf
Application Notes for related Tools & Software	https://www.st.com/resource/en/application_note/an5394-getting-started-with-projects-based-on-the-stm32l5-series-in-stm32cubeide-stmicroelectronics.pdf
Application Notes for related Tools & Software	https://www.st.com/resource/en/application_note/an5418-how-to-build-a-simple-usbp-d-sink-application-with-stm32cubemx-stmicroelectronics.pdf
Application Notes for related Tools & Software	https://www.st.com/resource/en/application_note/an5426-migrating-graphics-middleware-projects-from-stm32cubemx-540-to-stm32cubemx-550-stmicroelectronics.pdf
Application Notes for related Tools & Software	https://www.st.com/resource/en/application_note/an5564-getting-started-with-projects-based-on-dualcore-stm32wl-microcontrollers-in-stm32cubeide-stmicroelectronics.pdf
Application Notes for related Tools & Software	https://www.st.com/resource/en/application_note/an4865-lowpower-timer-lptim-applicative-use-cases-on-stm32-mcus-and-mpus-stmicroelectronics.pdf
Application Notes for related Tools & Software	https://www.st.com/resource/en/application_note/an5698-adapting-the-xcubestl-functional-safety-package-for-stm32-iec-61508-compliant-to-other-safety-standards-stmicroelectronics.pdf
Application Notes for related Tools & Software	https://www.st.com/resource/en/application_note/an5731-stm32cubemx-and-stm32cubeide-threadsafe-solution-stmicroelectronics.pdf
Application Notes for related Tools & Software	https://www.st.com/resource/en/application_note/an4502-stm32-smbuspmbus-expansion-package-for-stm32cube-stmicroelectronics.pdf
Application Notes for related Tools & Software	https://www.st.com/resource/en/application_note/an5952-how-to-use-cmake-in-stm32cubeide-stmicroelectronics.pdf
Errata Sheets	https://www.st.com/resource/en/errata_sheet/es0290-stm32f74xxx-and-stm32f75xxx-device-limitations-stmicroelectronics.pdf
Datasheet	https://www.st.com/resource/en/datasheet/dm00166116.pdf
Programming Manuals	https://www.st.com/resource/en/programming_manual/pm0253-stm32f7-series-and-stm32h7-series-cortexm7-processor-programming-manual-stmicroelectronics.pdf

Reference Manuals	https://www.st.com/resource/en/reference_manual/rm0385-stm32f75xxx-and-stm32f74xxx-advanced-armbased-32bit-mcus-stmicroelectronics.pdf
Technical Notes & Articles	https://www.st.com/resource/en/technical_note/tn1163-description-of-wlcsp-for-microcontrollers-and-recommendations-for-its-use-stmicroelectronics.pdf
Technical Notes & Articles	https://www.st.com/resource/en/technical_note/tn1204-tape-and-reel-shipping-media-for-stm32-microcontrollers-in-bga-packages-stmicroelectronics.pdf
Technical Notes & Articles	https://www.st.com/resource/en/technical_note/tn1205-tape-and-reel-shipping-media-for-stm8-and-stm32-microcontrollers-in-fpn-packages-stmicroelectronics.pdf
Technical Notes & Articles	https://www.st.com/resource/en/technical_note/tn1206-tape-and-reel-shipping-media-for-stm8-and-stm32-microcontrollers-in-qfp-packages-stmicroelectronics.pdf
Technical Notes & Articles	https://www.st.com/resource/en/technical_note/tn1207-tape-and-reel-shipping-media-for-stm8-and-stm32-microcontrollers-in-so-packages-stmicroelectronics.pdf
Technical Notes & Articles	https://www.st.com/resource/en/technical_note/tn1208-tape-and-reel-shipping-media-for-stm8-and-stm32-microcontrollers-in-tssop-and-ssop-packages-stmicroelectronics.pdf
Technical Notes & Articles	https://www.st.com/resource/en/technical_note/tn1433-reference-device-marking-schematics-for-stm32-microcontrollers-and-microprocessors-stmicroelectronics.pdf